


NOTES:

1. SUBSTRATE MATERIAL:
BOROFLOAT®
2. COATING (APPLY ACROSS CLEAR APERTURE)
- S1: NONE
S2: NONE
3. POWER, IRREGULARITY, SURFACE QUALITY, AND COATING
SPECIFICATIONS APPLY ACROSS CLEAR APERTURE

4. FINE GROUND SURFACE

5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	<div>Edmund Optics®</div>			
SHAPE	CONCAVE	PLANO				
EFFECTIVE FOCAL LENGTH	152.4mm	N/A	<div>THIRD ANGLE PROJECTION</div>	<div>TITLE</div>	<div>2" Dia, 6" FL Uncoated, Spherical Mirror</div>	
FOCAL LENGTH TOLERANCE	±2%	N/A				
APERTURE	f/3	N/A				
SURFACE QUALITY	60-40	60-40				
SURFACE FLATNESS	λ/4	λ/4				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	49597
						SHEET 1 OF 1