



NOTES:

1. SUBSTRATE: N-SF5
2. COATING
S1: NONE
S2: NONE
3. EDGES: FINE GROUND
4. CENTERING: 3-5 ARCMIN
5. ASPHERE FIGURE ERROR: 0.75 μm RMS

6. ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE)

$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS}) * Y^2}{1 + \sqrt{1 - (1+k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$




SECTION A-A

COEFFICIENT TABLE 6.

COEFFICIENT	S1
SEMI-DIAMETER	25.000000E+00
(1/RADIUS)	4.955156E-02
k	-9.514491E-01
D	0.000000E+00
E	6.256875E-06
F	2.852864E-09
G	-9.569919E-13
H	-2.302468E-15
J	0.000000E+00
L	0.000000E+00

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	EFL @587.6 : 30	Edmund Optics®		
SHAPE	CONVEX	CONVEX	BFL @587.6 : 18.04	 Edmund Optics® 50mm DIA., 0.83 NUMERICAL APERTURE UNCOATED, ASPHERIC LENS		
RADIUS	203181	INFINITY	THIRD ANGLE PROJECTION 			
SURFACE QUALITY	60-40	60-40	ALL DIMS IN	mm	DWG NO	67248
CLEAR APERTURE	90%	90%				SHEET 1 OF 1
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				