


**NOTES:**



1. SUBSTRATE:  
D-ZK3
2. NUMERICAL APERTURE: 0.15
3. COATING  
S1 & S2: R(ABS) < 1.0% @ 600 - 1050nm
4. FOCAL LENGTH TOLERANCE: ±1%
5. TRANSMITTED WAVEFRONT ERROR ( $\lambda$ , RMS): < 0.090



SECTION A-A

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	18.40	 <b>Edmund Optics®</b>		
			BFL	17.11			
SHAPE	CONVEX	PLANO	THIRD ANGLE PROJECTION		TITLE	0.15 NA 18.40mm FL 600-1050nm AR COATED, MOLDED ASPHERIC LENS	
SURFACE QUALITY	40-20	40-20	ALL DIMS IN	mm	DWG NO	87114	SHEET 1 OF 1
CLEAR APERTURE	Ø5.50	Ø5.50					
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					