


NOTES:

1. SUBSTRATE MATERIAL:
N-BK7
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2:
LASER V-COAT



R(abs) <0.25% @ 532nm
R(avg) <1.5% @ 495 - 570nm

3. FINE GROUND SURFACE
4. POWER, IRREGULARITY, AND SURFACE QUALITY
SPECIFICAIONS APPLY ACROSS CLEAR APERTURE
5. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	<div><div>EFL</div><div>100±3%</div></div> <div><div>BFL</div><div>(98.68)</div></div> <div><div> Edmund Optics®</div></div>			
SHAPE	CONVEX	PLANO				
RADIUS	51.68	∞	<div><div>THIRD ANGLE PROJECTION</div><div></div><div><div>TITLE</div><div>12.5mm DIA X 100.0mm FL 532nm V-COAT, CYLINDER LENS</div></div></div>			
SURFACE QUALITY	60-40	60-40				
CLEAR APERTURE	Ø 11.50	Ø 11.50	<div><div>ALL DIMS IN</div><div>mm</div><div><div>DWG NO</div><div>33226</div></div><div><div>SHEET</div><div>1 OF 1</div></div></div>			
COATING APERTURE	Ø 11.50	Ø 11.50				
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED				