

NOTES:

1. SUBSTRATE: SILICON (SI)

2. COATING

S1: R(avg) <3% @ 3 - 5µm
S2: R(avg) <3% @ 3 - 5µm



3. EDGES: DIAMOND TURNED

4. CENTERING, ETD: <21.8 µm

5. RoHS: COMPLIANT

6. ASPHERIC SURFACE DESCRIBED BY THE FOLLOWING
EQUATION AND COEFFICIENTS SHOWN IN TABLE BELOW

$$Z_{ASPH}(Y) = \frac{(1/RADIUS)^2 * Y^2}{1 + \sqrt{1 - (1+k) * (1/RADIUS)^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$



COEFFICIENT TABLE	
COEFFICIENT	S1
k	-1.712056E+00
D	0.000000E+00
E	0.000000E+00
F	0.000000E+00
G	0.000000E+00
H	0.000000E+00
J	0.000000E+00
L	0.000000E+00

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	CONVEX	CONCAVE
RADIUS	26.922	43.582
SURFACE ACCURACY	<0.3µm	N/A
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	90%	90%
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

EFL @ 4000nm: 25

BFL @ 4000nm: 22.5

THIRD ANGLE
PROJECTION

ALL DIMS IN mm



Edmund Optics®

TITLE

25mm DIA X 25mm FL 3-5µm AR COATED, SI
ASPHERIC LENS

DWG NO

89617

SHEET
1 OF 1