



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



ANGLE TOLERANCE (°)	±1 x ±4
DIFFUSING ANGLE (°)	0.2 x 40 (FWHM)
DAMAGE THRESHOLD, PULSED	0.22 J/cm ² @ 1064nm @ 10ns
OPERATING TEMPERATURE (°C)	-30 to +100 (Maximum of 240 Hours)
SUBSTRATE	POLYCARBONATE
TRANSMISSION (%)	>85
WAVELENGTH RANGE (nm)	400 - 1600
ROHS	COMPLIANT

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]

THIRD ANGLE PROJECTION 	TITLE	40° Diffusing Angle 8" x 8" Unmounted Sheet		
	DWG NO	65890	SHEET 1 OF 1	