




FOCAL LENGTH (EFL): $21 \pm 0,21$

BACK FOCAL LENGTH (BFL): 20,06

- 1 AR COATING: VIS 0°
R(AVG) $\leq 0,4\%$ FROM 425-675nm @ 0° AOI
- 2 BLACKENED SURFACE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$10,85 \pm 0,011$ CX	GLASS N-BK7 517/642	R	∞ PL
Øe	5,4		Øe	5,4
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

$\lambda = 587,6$ nm

FIRST ANGLE
PROJECTION



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm



Edmund Optics®

TITLE

6,0mm Dia, x 21,0mm FL, VIS 0, Inked,
Plano-Convex Lens

DWG NO

47465INK

SHEET SIZE
A4

SHEET
1 OF 1