





FOCAL LENGTH (EFL): 15 ±0,15
 BACK FOCAL LENGTH (BFL): 13,37

- 1 AR COATING: UV-AR
 $R(ABS) \leq 1,0\%$ FROM 250-425nm @ 0° AOI
 $R(AVG) \leq 0,75\%$ FROM 250-425nm @ 0° AOI
 $R(AVG) \leq 0,5\%$ FROM 370-420nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	13,01±0,013 CX	GLASS FUSED SILICA 458/678	R	13,01±0,013 CX
Øe	11		Øe	11
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics®				
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			TITLE 12mm Dia, x 15mm FL, UV-AR Coated, UV Double-Convex Lens				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			ALL DIMS IN: mm						
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING									
INDICATIONS IN ACCORDANCE WITH ISO 10110			DWG NO		49252		SHEET SIZE A4	SHEET 1 OF 1	