




FOCAL LENGTH (EFL): 20 ± 0,2  
BACK FOCAL LENGTH (BFL): 18,99

1 AR COATING: VIS 0°  
R(AVG) ≤ 0,4% FROM 425-675nm @ 0° AOI

| LEFT SURFACE |                          | MATERIAL             | RIGHT SURFACE |                          |
|--------------|--------------------------|----------------------|---------------|--------------------------|
| R            | 30,6±0,031 CX            | GLASS N-SF11 785/258 | R             | 30,6±0,031 CX            |
| Øe           | 14                       |                      | Øe            | 14                       |
| 3/           | 3 (0,5) λ=632,8 nm       |                      | 3/            | 3 (0,5) λ=632,8 nm       |
| 4/           | -                        |                      | 4/            | 1,27'                    |
| 5/           | 40 - 20 (MIL-PRF-13830B) |                      | 5/            | 40 - 20 (MIL-PRF-13830B) |
| 6/           | -                        |                      | 6/            | -                        |

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT  
SCALE: NONE λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

15mm Dia, x 20mm FL, VIS 0 Coated, Double-Convex Lens

DWG NO

63607

SHEET SIZE  
A4

SHEET  
1 OF 1