



FOCAL LENGTH (EFL): $15 \pm 0,15$
 BACK FOCAL LENGTH (BFL): $11,71$

1 AR COATING: 1064nm V-COAT
 R(ABS) < 0,25% @ 1064nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$10,09 \pm 0,01$ CX	GLASS N-SF5 673/322	R	∞ PL
Øe	14		Øe	14
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,49'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT
 SCALE: NONE
 $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

EO® Edmund Optics®

TITLE 15,0mm Diameter x 15,0mm FL, 1064nm V-Coat, PCX Lens

DWG NO 87617

SHEET SIZE A4 SHEET 1 OF 1