





FOCAL LENGTH (EFL): 25 ±0,25
BACK FOCAL LENGTH (BFL): 21,62

- 1 1064nm Laser AR Coating
R(ABS) < 0,25% @ 1064nm @ 0° AOI

LEFT SURFACE			MATERIAL	RIGHT SURFACE	
R 11,902 CX			GLASS Fused Silica 458/678	R ∞ PL	
Øe 11,7				Øe 11,7	
⌂ SEE NOTE 1				⌂ SEE NOTE 1	
3/ 2 (0,2) λ=632,8 nm				3/ 2 (0,2) λ=632,8 nm	
4/ -				4/ 2,18'	
5/ 10 - 5				5/ 10 - 5	
6/ 15J-cm ⁻² ; 1064nm; 20ns [20Hz]			6/ 15J-cm ⁻² ; 1064nm; 20ns [20Hz]		
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION		
ROHS: COMPLIANT	SCALE: NONE	λ = 355nm			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE 12,7mm Dia x 25mm FL, 1064nm Laser AR Coating, 15J Coated, Plano-Convex Lens	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING					
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO 38733
			SHEET SIZE A4		SHEET 1 OF 1