

NOTES:

1. SUBSTRATE: ALUMINUM
2. BEAM DEVIATION: 10 ARCSEC
RAY DEVIATION: 180°
3. COATING SPECIFICATION (APPLY ACROSS CLEAR APERTURE):



R(AVG) >94% @ 700 - 800nm

R(AVG) >97% @ 800 - 2000nm

R(AVG) >98% @ 2 - 12μm

4. SURFACE QUALITY: 60-40

5. WAVELENGTH RANGE: 700 - 12000nm




SECTION A-A
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

Edmund Optics®

25.4mm DIA., 10 ARCSEC, BARE GOLD
REPLICATED HOLLOW METAL
RETROREFLECTOR

THIRD ANGLE
PROJECTION



TITLE

ALL DIMS IN

mm

DWG NO

15902

SHEET
1 OF 1