




NOTES:

- 1. SUBSTRATE MATERIAL:
FLOAT GLASS
- 2. COATING (APFLOW ACROSS CLEAR APERTURE):
S1: GOLD
S2: NONE
- 3. BLAZE ANGLE: 8° 36'
NOMINAL BLAZE WAVELENGTH: 350-800nm
GROOVE DENSITY: 600 GROOVES/mm

4. EDGES GROUND

- 5. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

Edmund Optics®

600 GROOVES, 25x25mm, RULED GOLD HIGH
PERFORMANCE REFLECTION GRATING

	S1	S2
SHAPE	PLANO	PLANO
CLEAR APERTURE	22.5 x 22.5	22.5 x 22.5

THIRD ANGLE PROJECTION	
ALL DIMS IN	mm

TITLE	600 GROOVES, 25x25mm, RULED GOLD HIGH PERFORMANCE REFLECTION GRATING		
DWG NO	15776	SHEET	1 OF 1