

NOTES:



1. SUBSTRATE:
S-LAH64
2. CENTERING TOLERANCE (AT 587.6nm):
BEAM DEVIATION (HALF ANGLE): <3 arcmin
3. COATING (APPLY ACROSS COATING APERTURE)
S1: VIS (350-700nm)
Ravg < 0.5% @ 350 - 700nm @ ±30° AOI
Rabs < 1.5% @ 350 - 700nm @ ±30° AOI
S2: VIS (350-700nm)
Ravg < 0.5% @ 350 - 700nm @ ±30° AOI
Rabs < 1.5% @ 350 - 700nm @ ±30° AOI

4. EDGES: FINE GROUND

5. ASPHERIC FIGURE ERROR: 0.75 μm RMS

6. ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE):



$$Z_{ASPH}(Y) = \frac{(1/RADIUS) * Y^2}{1 + \sqrt{1 - (1+k) * (1/RADIUS)^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$



SECTION A-A

COEFFICIENT TABLE 6.

COEFFICIENT	S1
SEMI-DIAMETER	1.000000E+01
(1/RADIUS)	7.15307582E-02
k	-1.001000E+00
D	0.000000E+00
E	1.662800E-05
F	-4.509800E-09
G	-3.844600E-09
H	-6.070000E-10
J	2.042000E-16
L	0.000000E+00

	S1	S2	 Edmund Optics®			
SHAPE	CONVEX	PLANO	BFL @ 780nm: 14.00			
RADIUS	13.980	INFINITY				
SURFACE QUALITY	40-20	40-20				
CLEAR APERTURE	18 mm	18 mm	TITLE			
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	20mm Dia., 0.56 NA, 350-700nm Coated, NIR Aspheric Lens			
ALL DIMS IN			mm	DWG NO	16271	SHEET 1 OF 1