


NOTES:

- 1. SUBSTRATE: ACRYLIC V825
- 2. COATING
 - S1: NONE
 - S2: NONE
- 3. FOCAL LENGTH TOLERANCE: 1.5%
- 4. DESIGN WAVELENGTH (DWL): 550nm
- 5. RoHS COMPLIANT

FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL @ 550nm	7.32	 Edmund Optics®		
SHAPE	CONVEX	CONVEX	BFL @ 550nm	6.58			
RADIUS	6.86	6.86			TITLE	7mm Dia. x 7.32mm FL, Small Diameter Plastic Aspheric Lens	
SURFACE QUALITY	60-40	60-40					
CLEAR APERTURE	Ø 5.60	Ø 5.60					
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	15272	SHEET 1 OF 1