

[See all 1 Products in Family](#)

-18 to +18 diopters, VIS Coated, Manually Focus-Tunable Lens

See More by [Optotune](#)



Stock **#12-329** **5 In Stock**

-

1

+

A\$1,232⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$1,232.00 each
Need More?	Request Quote

Product Downloads

General	
Specialty Lens	Type:
>100,000	Lifecycles:
ML-20-37	Model Number:
Physical & Mechanical Properties	
39.50	Diameter (mm):

20	Clear Aperture CA (mm):
18.60	Thickness (mm):
Optical Properties	
Low Dispersion Polymer	Substrate: ☐
BBAR (400-700nm)	Coating:
400 - 700	Wavelength Range (nm):
65	Abbe Number (v _d):
-18 to +18 diopter -55 to +55mm	Focus Range (mm):
1.38	Index of Refraction (n _d):
0.25λ @ 525nm	Transmitted Wavefront Error, RMS:
10 kW/cm ² @ 1064nm	Damage Threshold, By Design: ☐
Threading & Mounting	
C-Mount (Female)	Mounting Threads:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Manually Adjustable Focal Length
- Concave to Convex Convertible Lens Shape
- BBAR Coating for Increased Performance Across Wavelength Range

Optotune Manually Focus Tunable Lenses are designed to have their lens curvature change between convex, flat, and concave by the rotation of the outer adjustment ring. This allows for the focal length of the lens to be tuned to the precise value required for an optical application. The rotation mechanism is extremely durable, providing a lifecycle greater than 100,000 rotations. Optotune Manually Focus Tunable Lenses provide a simple, cost-effective solution for applications where system parameters are still being decided, such as in system prototyping or R&D applications. These focus tunable lenses can also be used singularly as an adjustable eye relief or as a pair to build a variable beam expander.