

Optotune -2 to +3 Diopter, M26 x 0.706 to M26 x 0.706 Focus Tunable Lens | EL-16-40-TC-VIS-5D-M26

See More by [Optotune](#)



Stock **#35-087** 3-5 DAYS

-

1

+

A\$2,416.00

ADD TO CART

Qty 1+
A\$2,416.00
Volume Pricing
Request Quote

Get Product Downloads

Substrate: ☐ Low Dispersion Polymer

Coating: BBAR (420-950nm)

Type: Specialty Lens

Wavelength Range (nm): 420 - 950

Abbe Number (v_d): 100.00
Clear Aperture CA (mm): 16.00
Current (mA): -250 to 250
Dimensions (mm): 47.0 x 70.0
Driver: #88-940
Focus Range: -2 to +3 diopter -500 to +333mm
Index of Refraction n_d: 1.3
Lifecycles: 1,000,000,000
Model Number: EL-16-40-TC-VIS-5D-M26
Mounting Threads: M26 x 0.706 (Male) M26 x 0.706 (Female)
Operating Temperature (°C): -20 to +65
Power Consumption (W): 0 - 0.7
Response Time (ms): 5 (typical @ 30°C)
Settling Time (ms): 25 (typical @ 30°C)
Thickness (mm): 17.60
Transmitted Wavefront Error, RMS: Vertical: 0.25λ @ 525nm Horizontal: 0.50λ @ 525nm

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View