

LightPath 354059 | 6.33mm Dia., 0.19 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock **#83-693** 20+ In Stock

☐ [Other Coating Options](#)

-

1

+

A\$136⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	A\$136.00 each
Qty 11-49	A\$122.40 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

354059

Lightpath Lens Code:

Aspheric Lens

Type:

Physical & Mechanical Properties	
6.33 ±0.015	Diameter (mm):
5.20	Clear Aperture CA (mm):
1.73	Edge Thickness ET (mm):
2.35 ±0.05	Center Thickness CT (mm):
Protective as needed	Bevel:
Optical Properties	
14.00 @ 633nm	Effective Focal Length EFL (mm):
0.19	Numerical Aperture NA:
D-ZK3	Substrate: □
±1	Focal Length Tolerance (%):
633	Aspheric Design Wavelength (nm):
BBAR (350-700nm)	Coating:
R _{avg} ≤0.5% @ 350 - 700nm	Coating Specification:
60-40	Surface Quality:
2.63	f#:
350 - 700	Wavelength Range (nm):
12.600	Working Distance (mm):
Infinite	Conjugate Distance:
< 0.145	Transmitted Wavefront Error (λ, RMS):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

PRODUCT DETAILS

- Compact, Molded Aspheric Lens Design
- Improved Performance Compared to Doublet and Triplet Lenses
- Ideal for Laser Tools and Measurement Systems

LightPath® Laser Tool Molded Aspheric Lenses are designed to fulfill the needs of a variety of tools and measurement systems utilizing laser diodes, including leveling lasers, projectors, scanners, trackers, and gun sights. By utilizing a single aspheric lens, the need for a multi-lens system is eliminated, allowing for a more compact and robust design. Each aspheric lens is offered with various anti-reflection coatings for optimum transmission in the visible and NIR wavelength ranges. LightPath® Laser Tool Molded Aspheric Lenses’ anti-reflection coating options for each lens provides <1% average reflection over the entire design wavelength range. The lenses are offered in four different diameters: 3mm, 4.70mm, 6mm, and 6.33mm.

LASER OPTICS

MADE BY EDMUND OPTICS®



LEARN MORE