

[See all 24 Products in Family](#)

**TECHSPEC® 0.06X GoldTL™ Telecentric Lens (Mount Included)**



0.06X GoldTL™ Telecentric Lens (Mount Included)

Stock **#17-205** **2 In Stock**

⊖ 1 ⊕ **A\$8,716<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1+	<b>A\$8,716.00</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

GoldTL™ Series **Product Family:**

**#56-873**, Included **Stock No. of Mounting Clamp:**

Telecentric Lens **Type:**

Focusable Telecentric **Special Type of Lens:**

**Physical & Mechanical Properties**

Variable	<b>Iris Option:</b>
288.42	<b>Length (mm):</b>
288.42	<b>Length excluding Threads (mm):</b>
160.00	<b>Maximum Diameter (mm):</b>
5.54	<b>Weight (kg):</b>

## Optical Properties

108.2mm	<b>Horizontal Field of View, 1/1.8" Sensor:</b>
96.3mm	<b>Horizontal Field of View, 1/2" Sensor:</b>
9.00	<b>Maximum Image Circle (mm):</b>
0.005	<b>Numerical Aperture NA, Object Side:</b>
>65% @ 40 lp/mm	<b>Resolution, Image Space MTF @ f/10:</b>
12 (7)	<b>Number of Elements (Groups):</b>
0.0388	<b>Typical Telecentricity @ 588nm (°):</b>
0.614	<b>Typical Distortion @ 588nm (%):</b>
0.06X	<b>Primary Magnification PMAG:</b>
0.06	<b>Telecentric Lens Magnification:</b>
170 - 220	<b>Working Distance (mm):</b>
f/6 - f/25	<b>Aperture (f/#):</b>
N4 MgF <sub>2</sub>	<b>Coating:</b>
±129 at f/10 (20% @ 20 lp/mm)	<b>Depth of Field (mm):</b>
0.06X	<b>Magnification:</b>
VIS	<b>Lens Wavelength Range:</b>

## Sensor

1/1.8"	<b>Maximum Sensor Format:</b>
2.74	<b>Pixel Size (µm):</b>

## Threading & Mounting

M154 x 1.50 (Female)	<b>Filter Thread:</b>
C-Mount	<b>Mount:</b>

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
----------------------	------------------------------------

## Product Details


- High Resolution Telecentric Lens for Measurement and Gauging
- Up to 5 MegaPixels, 3.45µm Pixel Size Sensors
- Up to 2/3", C-Mount Telecentric Lens
- Magnification from 0.06X to 1X

TECHSPEC® GoldTL™ Telecentric Lenses were designed specifically for machine vision and metrology applications. The unique focusable design allows for working distance adjustment, while still providing <0.2° telecentricity. These lenses also feature high resolutions, low distortions, and are available for 1/2" or 2/3" sensors. TECHSPEC® GoldTL™ Telecentric Lenses have a front filter thread for easy integration of [color filters](#), [polarizers](#) or other mounted components. Both the iris and focusing adjustment positions can be fixed by set screws to remain secure in high vibration environments.

## Technical Information




**Telecentric Lens Mounts**



Units: mm

**Telecentric Lens Mount for #56-948**



Units: mm