

0.125" (X,Y,Z) Travel, XYZ Axes, Micro Series (A)



Stock #38-528 3-5 DAYS

1 **A\$1,163.20**

ADD TO CART

Qty 1+

A\$1,163.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:
Linear (X-Y-Z)

Guide System:
Ball Bearing

Type of Drive:
Fine Screw (80 Pitch)

Drive Orientation:
Center Drive

Type:
English

Stage Size (mm):
11.2 x 26.2

Travel (mm):
3.2

Travel (inches):
0.125

Center Hole:
0.155" (3.9mm) Thru with 8-32 TPI Threaded

Construction:
Aluminum Body, Stainless Steel Rails

Load Capacity, Normal (kg):
0.25

Note:
Without Covered Rails

Stage Size (inches):
0.44 x 1.03

Straight Line Accuracy (µm):
1

Weight (g):
9

Wobble (mrad):
0.01

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)
