

LightPath 354260 | 6.5mm Dia., 0.16 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#37-098** [CONTACT US](#)

[Other Coating Options](#)

⊖ 1 ⊕ **A\$136⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-10	A\$136.00 each
Qty 11-49	A\$122.40 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Thickness: 0.25 (t) (mm)
Material: BK7


Compatible Window:

354260	Lightpath Lens Code:
Aspheric Lens	Type:
Collimate or Focus Laser Light	Typical Applications:
Physical & Mechanical Properties	
6.50 ±0.015	Diameter (mm):
5	Clear Aperture CA (mm):
1.8	Edge Thickness ET (mm):
2.21 ±0.05	Center Thickness CT (mm):
Protective as needed	Bevel:
12.727	Distance from Window to Lens (D) (mm):
Optical Properties	
15.29 @ 780nm	Effective Focal Length EFL (mm):
0.16	Numerical Aperture NA:
D-ZK3	Substrate: <input type="checkbox"/>
±1	Focal Length Tolerance (%):
780	Aspheric Design Wavelength (nm):
BBAR (350-700nm)	Coating:
$R_{avg} \leq 0.5\%$ @ 350 - 700nm	Coating Specification:
40-20	Surface Quality:
3.12	f#:
350 - 700	Wavelength Range (nm):
13.98	Working Distance (mm):
Infinite	Conjugate Distance:
< 0.09	Transmitted Wavefront Error (λ, RMS):
Environmental & Durability Factors	
≤200	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:


PRODUCT DETAILS

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



TECHNICAL INFORMATION



COMPATIBLE MOUNTS
