

## 0.19X, High Resolution Inline Telecentric Lens



Stock #65-026 [CONTACT US](#)

1 [+](#) [-](#) A\$7,373<sup>00</sup>

[ADD TO CART](#)

### Volume Pricing

Qty 1+	A\$7,373.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

**Series:**  
High Res In-Line Illumination C-Mnt Telecentric Lenses

**Note:**  
Magnification Tolerance %: ±3

**Type:**  
Telecentric Lens

**Compatible Light Guide/Source:**  
1/4" (0.312")

**Type of Illumination:**  
In-Line Illumination

## Physical & Mechanical Properties

171.60 **Length (mm):**

80 **Maximum Diameter (mm):**

## Optical Properties

46.9mm **Horizontal Field of View, 2/3" Sensor:**

11.00 **Maximum Image Circle (mm):**

0.017 **Numerical Aperture NA, Object Side:**

4.00 **Resolving Power, Image Space ( $\mu\text{m}$ ):**

$\pm 3.00$  **Working Distance Tolerance (mm):**

0.19X **Primary Magnification PMAG:**

0.19 **Telecentric Lens Magnification:**

110.00 **Working Distance (mm):**

f/6 **Aperture (f/#):**

$\leq 0.02$  **Distortion (%):**

0.19X **Magnification:**

VIS **Lens Wavelength Range:**

## Sensor

2/3" **Maximum Sensor Format:**

2.60 **Pixel Size ( $\mu\text{m}$ ):**

## Threading & Mounting

N/A **Filter Thread:**

C-Mount **Mount:**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Designed for High Resolution Imaging
- In-line Illumination Port (0.312" Ferrule)
- 2/3" Max. Sensor Format

This line of high resolution telecentrics was designed to allow of in-line illumination. This make them ideal for applications that need intense and direct illumination. The coaxial port accepts 1/4" fiber bundles with a 0.312" ferrule diameter, which readily connects to our wide selection of light guides and illuminators.

The lenses feature a standard C-Mount threading to connect to the most common 2/3" and smaller machine vision cameras. Designed to have  $\pm 0.05\%$  distortion, these lenses are perfect for challenging measurement applications.