

0.2 OD, 25mm Dia., NIR I Coated, Absorptive ND Filter

See More by [Hoya](#)



Anti-Reflection (AR) Coated HOYAAbsorptive Neutral Density (ND) Filters

Stock #13-165 3-5 DAYS

-

1

+

A\$116.80

ADD TO CART

Qty 1-10
A\$116.80
Qty 11+
A\$104.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
25.00

Optical Density OD (Average):
0.2 ±0.04 @ 400-700nm (Uncoated Filter)

Nominal Optical Density @ Center of Coating:
0.26 @ 900nm

Glass/Filter Number: Hoya ND-50
Substrate: ☐ ND Filter Glass
Coating: NIR I (600-1050nm)
Index of Refraction n_d: 1.50
Surface Quality: 80-50
Transformation Temperature (°C): 495
Thickness (mm): 1.50
Thickness Tolerance (mm): ±0.5
Transmission (%): 63.0 (average) @ 400 - 700nm
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 400 - 700
Dimensional Tolerance (mm): ±0.1
Parallelism (mm): <0.02
Coating Specification: R_{avg} ≤0.5% @ 600 - 1050nm
Wavelength Range (nm): 600 - 1050
Stock No. of Uncoated Filter: #63-461

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant