

LightPath 354058 | 6.33mm Dia., 0.22 NA, Uncoated, Molded Aspheric Lens

See More by [Lightpath®](#)



Stock **#83-688** CLEARANCE 3-5 DAYS
[Other Coating Options](#)

-

1

+

A\$27.12

ADD TO CART

Qty 1+
A\$27.12

Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
6.33 ±0.015

Effective Focal Length EFL (mm):
12.00 @633nm

Numerical Aperture NA:
0.22

Substrate: [D-ZK3](#)

Focal Length Tolerance (%):

±1
Aspheric Design Wavelength (nm): 633
Coating: Uncoated
Surface Quality: 60-40
Clear Aperture CA (mm): 5.20
Edge Thickness ET (mm): 1.67
Center Thickness CT (mm): 2.40 ±0.05
f#: 2.27
Bevel: Protective bevel as needed
Lightpath Lens Code: 354058
Type: Aspheric Lens
Wavelength Range (nm): 350 - 2400
Working Distance (mm): 10.600
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
