


0.1" Scale/100 Div, 19mm Dia. Eyepiece Reticle



Stock **#62-051** **2 In Stock**

-

1

+

A\$286^{.40}

ADD TO CART

Volume Pricing	
Qty 1-4	A\$286.40 each
Qty 5+	A\$274.08 each
Need More?	Request Quote

Product Downloads

General

No

NIST Certification:

Physical & Mechanical Properties

19.00 +0.0/-0.1

Diameter (mm):

±3

Overall Accuracy (µm):

0.0025

Line Width (mm):

0.1	Centering (mm):
±0.0015	Line Width Tolerance (mm):
Optical Properties	
B270	Substrate: ☐
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:

Product Details

- Designed for 1XObjective Power
- 1, 5, or 10mm Scale Versions
- 0.1 or 0.5 Inch Scale Versions

Reticles are clear glass discs marked with scales or patterns, which fit into microscope eyepieces at the internal real image plane. This is the intermediate image of the specimen/object under inspection produced by the objective lens of the microscope. By placing the reticle at this position, the scale/pattern is superimposed on the image and both are in simultaneous focus. These reticles are all designed for an objective power of 1X.