

[See all 19 Products in Family](#)

0.22 NA UV/VIS Patchcord 100 Micron Fiber w/ FC Connector



Stock #23-705 **2 In Stock**

− 1 + A\$315²⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-4 | A\$315.20 each |
| Qty 5-10 | A\$283.20 each |
| Qty 11-24 | A\$252.80 each |
| Need More? | Request Quote |

Product Downloads

General

Patchcord **Type:**
Multimode **Fiber Cable Type:**

Physical & Mechanical Properties

1.5 **Length (m):**

Core Diameter (µm):
100

Jacket Material:
PVC MONOCOIL (0.112" OD)

Optical Properties

Coating Type:
Nylon

Numerical Aperture NA:
0.22

Wavelength:
UV-VIS

Hardware & Interface Connectivity

Connector:
FC/PC

Environmental & Durability Factors

Operating Temperature (°C):
-40 to +100

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 250:
[Compliant](#)

Product Details

- UV/VIS and VIS/NIR Versions Available
- FC Connector Compatible with [Spatial Filters](#)
- FC Connector Compatible with [Fiber Alignment Mounts](#)
- FC and SMA Connector Options

High Quality Fiber Patchcords are designed for UV-VIS (190 - 1250nm) or VIS-NIR (300 - 2400nm) ranges. These Patchcords are 1.5 meters in length with Nylon or Tefzel coatings. With core diameters ranging from 50 – 1000µm, these patchcords provide quality solutions for a variety of core sizes. High Quality Fiber Patchcords are available with SMA905 or FC/PC connectors featuring a 0.22 numerical aperture. These Patchcords are ideal for applications requiring optimum transmission in the UV-VIS or VIS-IR wavelengths.

Technical Information

