

[See all 19 Products in Family](#)

## 0.22 NA VIS/NIR Patchcord 200 Micron Fiber w/ SMA Connector



Stock #23-692 **6 In Stock**

A\$315<sup>20</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	A\$315.20 each
Qty 5-10	A\$283.20 each
Qty 11-24	A\$246.40 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Patchcord Type:

Multimode Fiber Cable Type:

#### Physical & Mechanical Properties

1.5 Length (m):

Core Diameter (µm):  
200

Jacket Material:  
PVC MONOCOIL (0.112" OD)

## Optical Properties

Coating Type:  
Nylon

Numerical Aperture NA:  
0.22

Wavelength:  
VIS-IR

## Hardware & Interface Connectivity

Connector:  
SMA905

## Environmental & Durability Factors

Operating Temperature (°C):  
-40 to +100

## Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Certificate of Conformance:  
[View](#)

Reach 250:  
[Compliant](#)

## Product Details

- UV/MS and VIS/NIR Versions Available
- FC Connector Compatible with [Spatial Filters](#)
- FC Connector Compatible with [Fiber Alignment Mounts](#)
- FC and SMA Connector Options

High Quality Fiber Patchcords are designed for UV-MS (190 - 1250nm) or VIS-NIR (300 - 2400nm) ranges. These Patchcords are 1.5 meters in length with Nylon or Tefzel coatings. With core diameters ranging from 50 – 1000µm, these patchcords provide quality solutions for a variety of core sizes. High Quality Fiber Patchcords are available with SMA905 or FC/PC connectors featuring a 0.22 numerical aperture. These Patchcords are ideal for applications requiring optimum transmission in the UV-VIS or VIS-IR wavelengths.

## Technical Information

