

TECHSPEC® 0.238X, 35mm M58 x 0.75 TitanTL® Telecentric Lens



TitanTL® Telecentric Lens

Stock **#34-037** [CONTACT US](#)

⊖ 1 ⊕

A\$10,861.00

ADD TO CART

Qty 1+
A\$10,861.00

Volume Pricing
Request Quote

Get Product Downloads

Numerical Aperture NA, Object Side:
0.0074

Horizontal Field of View, 35mm Sensor:
151.3mm

Number of Elements (Groups):
7 (5)

Note:
TitanTL®

Type:
Telecentric Lens

Primary Magnification PMAG: 0.238X
Maximum Sensor Format: 35mm
Working Distance (mm): 267
Mount: M58 x0.75
Aperture (f/#): f/16
Coating: λ/4 MgF ₂
Depth of Field (mm): ±14.6mm (20% @ 20 lp/mm, f/16)
FOV @ Max Sensor Format, H x V (mm): 151.3 x 100.9
Rear Filter Diameter (mm): 50.8
Typical Distortion @ 520nm (%): <0.2
Typical Telecentricity @ 520nm (°): <0.1
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View