

LightPath 354062 | 6mm Dia., 0.24 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock **#83-705**

CLEARANCE

3-5 DAYS

Other Coating Options

-

1

+

A\$36.72

ADD TO CART

Qty 1+

A\$36.72

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
6.00 ±0.015

Effective Focal Length EFL (mm):
11.00 @633nm

Numerical Aperture NA:
0.24

Substrate:

D-ZK3

Focal Length Tolerance (%):

±1
Aspheric Design Wavelength (nm): 633
Coating: BBAR (350-700nm)
Coating Specification: R _{avg} ≤0.5% @ 350 - 700nm
Surface Quality: 100-60
Clear Aperture CA (mm): 5.20
Edge Thickness ET (mm): 1.53
Center Thickness CT (mm): 2.25 ±0.05
f/#: 2.08
Bevel: Protective bevel as needed
Lightpath Lens Code: 354062
Type: Aspheric Lens
Wavelength Range (nm): 350 - 700
Working Distance (mm): 9.700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant