

[See all 19 Products in Family](#)

## 0.22 NA VIS/NIR Patchcord 600 Micron Fiber w/ SMA Connector



Stock #23-700 **3 In Stock**

- 1 + A\$444.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	A\$444.80 each
Qty 5-10	A\$400.00 each
Qty 11-24	A\$356.80 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Patchcord **Type:**  
Multimode **Fiber Cable Type:**

#### Physical & Mechanical Properties

1.5 **Length (m):**

600 Core Diameter (µm):

PVC MONOCOIL (0.190" OD) Jacket Material:

## Optical Properties

Nylon Coating Type:

0.22 Numerical Aperture NA:

VIS-IR Wavelength:

## Hardware & Interface Connectivity

SMA905 Connector:

## Environmental & Durability Factors

-40 to +100 Operating Temperature (°C):

## Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 250:

## Product Details

- UV/MS and VIS/NIR Versions Available
- FC Connector Compatible with [Spatial Filters](#)
- FC Connector Compatible with [Fiber Alignment Mounts](#)
- FC and SMA Connector Options

High Quality Fiber Patchcords are designed for UV-VIS (190 - 1250nm) or VIS-NIR (300 - 2400nm) ranges. These Patchcords are 1.5 meters in length with Nylon or Tefzel coatings. With core diameters ranging from 50 – 1000µm, these patchcords provide quality solutions for a variety of core sizes. High Quality Fiber Patchcords are available with SMA905 or FC/PC connectors featuring a 0.22 numerical aperture. These Patchcords are ideal for applications requiring optimum transmission in the UV-VIS or VIS-IR wavelengths.

## Technical Information

