

LightPath 354064 | 6mm Dia., 0.24 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#37-109** CLEARANCE 3-5 DAYS

[Other Coating Options](#)

- 1 +

A\$47.92

ADD TO CART

Qty 1+

A\$47.92

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
6.00 ±0.015

Effective Focal Length EFL (mm):
11.00 @ 633nm

Numerical Aperture NA:
0.24

Substrate: [D-ZK3](#)

Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 633
Coating: BBAR (350-700nm)
Coating Specification: R _{avg} ≤0.5% @ 350 - 700nm
Surface Quality: 80-50
Clear Aperture CA (mm): 5.2
Edge Thickness ET (mm): 2.59
Center Thickness CT (mm): 3.10 ±0.05
f/#: 2.50
Bevel: Protective bevel as needed
Compatible Window: Thickness: 0.25 (t) (mm) Material: BK7
Distance from Window to Lens (D) (mm): 8.706
Lightpath Lens Code: 354064
Operating Temperature (°C): ≤200
Type: Aspheric Lens
Wavelength Range (nm): 350 - 700
Typical Applications: Collimate or Focus Laser Light
Working Distance (mm): 9.3
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant