

**TECHSPEC® 0.28X, 2/3" C-Mount PlatinumTL™ Telecentric Lens**



0.28X Magnification, #62-933

Stock **#62-933 4 In Stock**

⊖ 1 ⊕ **A\$3,227<sup>00</sup>**

**ADD TO CART**

Volume Pricing

Qty 1+	<b>A\$3,227.00</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

PlatinumTL™ Series **Series:**

**Stock No. of Mounting Clamp:**  
#63-442 Sold Separately

Telecentric Lens **Type:**

**Physical & Mechanical Properties**

Variable **Iris Option:**

203.80	<b>Length (mm):</b>
60.5	<b>Maximum Diameter (mm):</b>
736	<b>Weight (g):</b>
17.5	<b>Flange Distance (mm):</b>
<b>Optical Properties</b>	
31.8mm	<b>Horizontal Field of View, 2/3" Sensor:</b>
22.9mm	<b>Horizontal Field of View, 1/2" Sensor:</b>
11.00	<b>Maximum Image Circle (mm):</b>
0.023	<b>Numerical Aperture NA, Object Side:</b>
10 (7)	<b>Number of Elements (Groups):</b>
<0.030	<b>Typical Telecentricity @ 588nm (°):</b>
<0.006	<b>Typical Distortion @ 588nm (%):</b>
0.28X	<b>Primary Magnification PMAG:</b>
0.28	<b>Telecentric Lens Magnification:</b>
180.00	<b>Working Distance (mm):</b>
31.4 x 23.6	<b>FOV @ Max Sensor Format, H x V (mm):</b>
f/6 - f/22	<b>Aperture (f/#):</b>
425 - 675nm BBAR	<b>Coating:</b>
±6.9mm at f/10 (20% @20 lp/mm)	<b>Depth of Field (mm):</b>
0.28X	<b>Magnification:</b>
VS	<b>Lens Wavelength Range:</b>

<b>Sensor</b>	
2/3"	<b>Maximum Sensor Format:</b>
2.74	<b>Pixel Size (µm):</b>

<b>Threading &amp; Mounting</b>	
M58 x 0.75 (Female)	<b>Filter Thread:</b>
C-Mount	<b>Mount:</b>


<b>Regulatory Compliance</b>	
<a href="#">View</a>	<b>Certificate of Conformance:</b>

## Product Details


- High Resolution f/6 Bi-Telecentric Lens for Measurement
- Up to 35 MegaPixels, 2.8µm Pixel Size Sensors
- APS-C, C-Mount, T-Mount, F-Mount Telecentric Lens
- Magnification from 0.28X to 1.7X

TECHSPEC® PlatinumTL™ Telecentric Lenses are designed for semiconductor and electronics inspection, measurement, and gauging applications. The precision designs feature high telecentricity (<0.1°), low distortion (<0.1%), and high light throughput with an adjustable aperture that achieves f/6 when fully open. Capable of supporting large format 28.7mm diagonal sensors, these lenses are compatible with the Sony IMX342 APS-C sensor and other similar format sensors such as the Sony IMX530. TECHSPEC® PlatinumTL™ Telecentric Lenses produce unparalleled levels of contrast yielding maximum image quality with the highest degree of measurement accuracy. These lenses are suitable for high vibration environments and feature a removable recessed set screw for securing the iris in place.


## Technical Information




#62-933, 0.28X, 2/3" C-Mount PlatinumTL™ Telecentric Lens, Distortion Plot



#62-933, 0.28X, 2/3" C-Mount PlatinumTL™ Telecentric Lens, Relative Illumination Plot




#62-933, 0.28X, 2/3" C-Mount PlatinumTL™ Telecentric Lens, Telecentricity Plot




#62-933, 0.28X, 2/3" C-Mount PlatinumTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 180mm Working Distance, f6



#62-933, 0.28X, 2/3" C-Mount PlatinumTL™ Telecentric Lens, Depth of Field Plot, 180mm Working Distance, f6



#62-933, 0.28X, 2/3" C-Mount PlatinumTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 180mm Working Distance, f10



#62-933, 0.28X, 2/3" C-Mount PlatinumTL™ Telecentric Lens, Depth of Field Plot, 180mm Working Distance, f10

Description		Stock No.	Flange	Length (A)	Front Diameter (B)	Back Diameter (C)
0.28X	C-Mount	<a href="#">#62-933</a>	17.5mm	230.8mm	60.5mm	33.5mm
0.5X	C-Mount	<a href="#">#62-932</a>	17.5mm	174.9mm	50mm	33.5mm
1.7X	C-Mount	<a href="#">#63-232</a>	17.5mm	189.5mm	60mm	46mm
0.28X	F-Mount	<a href="#">#62-922</a>	46.5mm	167.6mm	138.6mm	55mm
	M42 x 1.0	<a href="#">#62-923</a>	6.56mm	208.5mm	138.6mm	50mm
	M42 x 1.0	<a href="#">#62-924</a>	19.53mm	195.5mm	138.6mm	50mm
0.5X	F-Mount	<a href="#">#62-912</a>	46.5mm	143mm	90mm	55mm
	M42 x 1.0	<a href="#">#62-913</a>	6.56mm	184mm	90mm	50mm
	M42 x 1.0	<a href="#">#62-914</a>	19.53mm	171.1mm	90mm	50mm
0.9X	F-Mount	<a href="#">#62-902</a>	46.5mm	170.8mm	65mm	55mm
	M42 x 1.0	<a href="#">#62-903</a>	6.56mm	210.7mm	65mm	53mm
	M42 x 1.0	<a href="#">#62-904</a>	19.53mm	197.8mm	65mm	53mm

