

TECHSPEC® 0.368X, 35mm M42 x 1.0 TitanTL® Telecentric Lens



TitanTL® Telecentric Lens

Stock **#34-026** 3-5 DAYS

⊖ 1 ⊕ **A\$7,004.00**

ADD TO CART

Qty 1+

A\$7,004.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Numerical Aperture NA, Object Side:
0.0115

Number of Elements (Groups):
7 (5)

Note:
TitanTL®

Type:
Telecentric Lens

Primary Magnification PMAG:
0.368X

Maximum Sensor Format: APS-H
Working Distance (mm): 169
Mount: M42 x 1.0
Aperture (f/#): f/16
Coating: N4 MgF ₂
Depth of Field (mm): ±6.6mm (20% @ 20 lp/mm, f/16)
Horizontal Field of View, APS-H Sensor: 79.3mm
FOV @ Max Sensor Format, H x V (mm): 79.3 x 54.9
Rear Filter Diameter (mm): 50.8
Typical Distortion @ 520nm (%): <0.2
Typical Telecentricity @ 520nm (°): <0.036
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View