

TECHSPEC® 0.40X SilverTL™ Telecentric Lens



0.40X Magnification



Stock **#56-677** ☐ In Stock

1 **A\$900.00**

ADD TO CART

Qty 1+

A\$900.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Length excluding Threads (mm):
159.00

Horizontal Field of View, 1/2" Sensor:
16mm

Filter Thread:
M43 x0.75 (Female)

Maximum Diameter (mm):
45.00

Weight (g): 228
Horizontal Field of View, 1/3" Sensor: 12mm
Numerical Aperture NA, Object Side: 0.033
Working Distance Tolerance (mm): ±3
Stock No. of Mounting Clamp: #56-870 Sold Separately
Resolution, Image Space MTF @ f/10: >40% @ 40 lp/mm
Number of Elements (Groups): 7 (4)
Note: SilverTL™
Horizontal Field of View, 1/1.8" Sensor: 18mm
Typical Telecentricity @ 588nm (°): <0.015
Typical Distortion @ 588nm (%): <0.020
Type: Telecentric Lens
Primary Magnification PMAG: 0.4X
Maximum Sensor Format: 1/1.8"
Working Distance (mm): 103.00
Mount: C-Mount
Aperture (f/#): f/6 - f/22
Coating: 425 - 675nm BBAR
Construction: Anodized Aluminum
Depth of Field (mm): ±3.0 at f/10 (20% @ 20 lp/mm)
FOV @ Max Sensor Format, H x V (mm): 18.0 x 13.5
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View