

[See all 4 Products in Family](#)

## 0.50 NA Patchcord 600 Micron Fiber w/ SMA Connector



Stock **#28-742** **1 In Stock**

A\$505<sup>.60</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	A\$505.60 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Patchcord **Type:**

### Physical & Mechanical Properties

**Minimum Bend Radius (mm):**  
43 (Short Term)  
86 (Long Term)

**Length (m):**  
1.5

### Optical Properties

0.50 **Numerical Aperture NA:**

VIS-NIR **Wavelength:**

300 - 1200 **Wavelength Range (nm):**

## Hardware & Interface Connectivity

SMA905 **Connector:**

## Environmental & Durability Factors

-40 to +85 **Operating Temperature (°C):**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 233:**

## Product Details

- 420 - 900nm Illumination with Converted LED
- Up to 20mW Output Power from a 1mm Multimode Fiber
- Light Coupling with **50µm – 1mm** Core Diameter Multimode Fibers
- Ideal for Spectroscopy Applications

The Fiber Coupled Broadband LED Light Source utilizes a VIS/NIR phosphor converter to convert the output of a 450nm LED chip into a broad 420 – 900nm spectrum. This light source provides highly efficient coupling with SMA connected multimode fibers with diameters of 50µm to 1mm and a numerical aperture (NA) up to 0.50, and features an output up to 20mW with a 1mm, 0.5 NA fiber. Featuring a built-in microprocessor, this light source can also be operated as a free-running stroboscope with an adjustable duty cycle and frequency up to 1kHz. The Fiber Coupled Broadband LED Light Source is a powerful alternative to halogen light sources and is ideal for VIS/NIR spectroscopy applications such as protein characterization, oxygen monitoring in marine ecosystems, and respiratory gas analysis. This light source can be controlled manually with the multifunctional rotating knob, directly via programming through a serial RS232 interface or with the provided user-friendly software interface.