

LightPath 354105 | 7.2mm Dia., 0.56 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-146** 3-5 DAYS

[Other Coating Options](#)

- 1 +

A\$152.00

ADD TO CART

Qty 1-10
A\$152.00
Qty 11+
A\$133.60
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
7.20 ±0.020

Effective Focal Length EFL (mm):
5.50 @ 633nm

Numerical Aperture NA:
0.60

Substrate: D-ZK3
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 633
Coating: BBAR (600-1050nm)
Coating Specification: R _{abs} <1.0% @ 600 - 1050nm
Surface Quality: 40-20
Clear Aperture CA (mm): 6
Edge Thickness ET (mm): 1.29
Center Thickness CT (mm): 2.94 ±0.03
f/#: 0.89
Bevel: Protective bevel as needed
Compatible Window: Thickness: 0.25 (t) (mm) Material: BK7
Distance from Window to Lens (D) (mm): 3.091
Lightpath Lens Code: 354105
Operating Temperature (°C): ≤200
Type: Aspheric Lens
Wavelength Range (nm): 600 - 1050
Typical Applications: Collimate or Focus Laser Light
Working Distance (mm): 3.7
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant