

TECHSPEC®

0.5X, 2/3" C-Mount PlatinumTL™ Telecentric Lens



0.5X Magnification, #62-932

Stock **#62-932** 3-5 DAYS

-

1

+

A\$2,364.00

ADD TO CART

Qty 1+
A\$2,364.00
Volume Pricing
Request Quote

Get Product Downloads

Length (mm):
174.90

Horizontal Field of View, 1/2" Sensor:
12.8mm

Horizontal Field of View, 2/3" Sensor:
17.7mm

Filter Thread:
M46 x0.75 (Female)

Maximum Diameter (mm):
50.0

Weight (g): 432
Numerical Aperture NA, Object Side: 0.041
Stock No. of Mounting Clamp: #63-442 Sold Separately
Flange Distance (mm): 17.5
Number of Elements (Groups): 10 (7)
Typical Telecentricity @ 588nm (°): <0.050
Typical Distortion @ 588nm (%): <0.006
Type: Telecentric Lens
Primary Magnification PMAG: 0.5X
Maximum Sensor Format: 2/3"
Working Distance (mm): 173.00
Mount: C-Mount
Aperture (f/#): f/6 - f/22
Coating: 425 - 675nm BBAR
Depth of Field (mm): ±2.1 at f/10 (20% @ 20 lp/mm)
FOV @ Max Sensor Format, H x V (mm): 17.6 x 13.2
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View