

**TECHSPEC® 0.8X, 65mm WD, In-Line CompactTL™ Telecentric Lens**



65mm WD, 0.8X, In-Line Version (Left) and MS Version (Right)



Stock #67-311 **12 In Stock**

⊖ 1 ⊕ **A\$805<sup>00</sup>**

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | <b>A\$805.00</b> each         |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**General**

CompactTL™ Series **Product Family:**  
 Edmund Optics® **Manufacturer:**  
 Telecentric Lens **Type:**  
**Compatible Light Guide/Source:**  
 1/4" (0.312") and 1/8" (0.187")

In-Line Illumination **Type of Illumination:**

## Physical & Mechanical Properties

Fixed **Iris Option:**

89.92 **Length (mm):**

89.92 **Length excluding Threads (mm):**

22.0 **Maximum Diameter (mm):**

55 **Weight (g):**

## Optical Properties

11mm **Horizontal Field of View, 2/3" Sensor:**

8mm **Horizontal Field of View, 1/2" Sensor:**

6mm **Horizontal Field of View, 1/3" Sensor:**

11.00 **Maximum Image Circle (mm):**

0.027 **Numerical Aperture NA, Object Side:**

±1 **Working Distance Tolerance (mm):**

5 (4) **Number of Elements (Groups):**

0.22 **Typical Telecentricity @ 588nm (°):**

0.0261 **Typical Distortion @ 588nm (%):**

0.8X **Primary Magnification PMAG:**

0.80 **Telecentric Lens Magnification:**

65 **Working Distance (mm):**

11.0 x 8.2 **FOV @ Max Sensor Format, H x V (mm):**

f/14.9 **Aperture (f/#):**

M4 MgF<sub>2</sub> **Coating:**

±1.2mm (20% @ 20 lp/mm) **Depth of Field (mm):**

0.8X **Magnification:**

VIS **Lens Wavelength Range:**

## Sensor

2/3" **Maximum Sensor Format:**

4.50 **Pixel Size (µm):**

## Threading & Mounting

M25.5 x 0.50 (Female) **Filter Thread:**

[#88-212 \(Required\)](#) **Filter Thread Adapter:**

M20 x 0.5 (Female) **Front Thread:**

C-Mount **Mount:**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**


[View](#) **Certificate of Conformance:**

## Product Details


- 2/3", C-Mount Telecentric Lens
- Up to 2.3 MegaPixels, 4.5µm Pixel Size Sensors
- Small Telecentric Lens with Coaxial Illumination Options

TECHSPEC® CompactTL™ Telecentric Lenses are designed for applications with tight space constraints due to their ultra-compact design. These lenses feature a 2/3" sensor format and a variety of different working distance and magnification options. From single unit to high volume implementation, these lenses provide a great price to performance ratio. TECHSPEC® CompactTL™ Telecentric Lenses are perfect for integration into gauging systems due to their excellent telecentricity and low distortion. The fixed iris and lockable focus make these lenses ideal for implementation into factory floors and assembly lines, as they will remain fixed over time.


## Technical Information




#67-311, 0.8X, 65mm WD, In-Line CompactTL™ Telecentric Lens, Distortion Plot




#67-311, 0.8X, 65mm WD, In-Line CompactTL™ Telecentric Lens, Relative Illumination Plot



#67-311, 0.8X, 65mm WD, In-Line CompactTL™ Telecentric Lens, Telecentricity Plot



#67-311, 0.8X, 65mm WD, In-Line CompactTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 65mm Working Distance, f14.9



#67-311, 0.8X, 65mm WD, In-Line CompactTL™ Telecentric Lens, Depth of Field Plot, 65mm Working Distance, f14.9