

[See all 4 Products in Family](#)

0.60 NA, 2.59mm FL, RPO VIS Molded Glass Aspheric Lens



Stock **#73-661** 20+ In Stock

-

1

+

A\$217^{.60}

ADD TO CART

Volume Pricing	
Qty 1+	A\$217.60 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens

Type:

Physical & Mechanical Properties

4.40 ±0.025

Diameter (mm):

3.12

Clear Aperture CA (mm):

3.06

Center Thickness CT (mm):

Bevel:

Protective as needed

Optical Properties	
2.59	Effective Focal Length EFL (mm):
0.60	Numerical Aperture NA:
H-ZLaF50B	Substrate: ☐
633	Aspheric Design Wavelength (nm):
BBAR (400 - 600nm)	Coating:
R _{avg} <1% @ 400 - 600nm	Coating Specification:
60-40	Surface Quality:
0.59	f/#:
400 - 600	Wavelength Range (nm):
1.19	Working Distance (mm):

Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Precision Visible Glass Molded Lenses
- Ideal for High Volume Production Requirements
- Multiple Glass Substrates Available

Rochester Precision Optics (RPO) Visible Molded Glass Aspheric Lenses offer several key benefits, including high precision, >99% transmission, and improved performance by reducing optical aberrations, leading to smaller spot sizes and sharper images. Cost-effective molding processes enable options for high-quantity OEM integration while maintaining consistent specifications. Rochester Precision Optics (RPO) Visible Molded Glass Aspheric Lenses are available with various focal lengths and numerical apertures and are AR coated for >99% transmission from 400 - 600nm. Their lightweight form factor, small diameter, and reduced thickness allow these molded aspheric lenses to be integrated into cameras, aerospace systems, measurement systems, biomedical instrumentation, and handheld optical tools.