

[See all 24 Products in Family](#)

TECHSPEC®

0.73X 1/2" GoldTL™ Telecentric Lens



#58-256 (0.73X)

Stock **#58-256** **2 In Stock**

-

1

+

A\$2,842⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$2,842.00 each
Need More?	Request Quote

Product Downloads

General	
GoldTL™ Series	Product Family:
#56-024 Sold Separately	Stock No. of Mounting Clamp:
Telecentric Lens	Type:
Focusable Telecentric	Special Type of Lens:

Physical & Mechanical Properties

Variable	Iris Option:
200.10	Length (mm):
200.10	Length excluding Threads (mm):
68.00	Maximum Diameter (mm):
1.1	Weight (kg):

Optical Properties	
9.9mm	Horizontal Field of View, 1/1.8" Sensor:
8.8mm	Horizontal Field of View, 1/2" Sensor:
9.00	Maximum Image Circle (mm):
0.061	Numerical Aperture NA, Object Side:
>65% @ 40 lp/mm	Resolution, Image Space MTF @ f/10:
10 (7)	Number of Elements (Groups):
<0.003	Typical Telecentricity @ 588nm (°):
0.100	Typical Distortion @ 588nm (%):
0.73X	Primary Magnification PMAG
0.73	Telecentric Lens Magnification:
98 - 123	Working Distance (mm):
9.9 x 7.4	FOV @ Max Sensor Format, H x V (mm):
f/6 - f/19.5	Aperture (f/#):
N4 MgF ₂	Coating:
±0.95 at f/10 (20% @ 20 lp/mm)	Depth of Field (mm):
0.73X	Magnification:
VIS	Lens Wavelength Range:

Sensor	
1/1.8"	Maximum Sensor Format:
2.74	Pixel Size (µm):

Threading & Mounting	
M62 x 0.75 (Female)	Filter Thread:
C-Mount	Mount:


Regulatory Compliance	
View	Certificate of Conformance:

Product Details


- High Resolution Telecentric Lens for Measurement and Gauging
- Up to 5 MegaPixels, 3.45µm Pixel Size Sensors
- Up to 2/3", C-Mount Telecentric Lens
- Magnification from 0.06X to 1X

TECHSPEC® GoldTL™ Telecentric Lenses were designed specifically for machine vision and metrology applications. The unique focusable design allows for working distance adjustment, while still providing <0.2° telecentricity. These lenses also feature high resolutions, low distortions, and are available for ½" or 2/3" sensors. TECHSPEC® GoldTL™ Telecentric Lenses have a front filter thread for easy integration of [color filters](#), [polarizers](#) or other mounted components. Both the iris and focusing adjustment positions can be fixed by set screws to remain secure in high vibration environments.


Technical Information




#58-256, 0.73X ½" GoldTL™ Telecentric Lens, Distortion Plot




#58-256, 0.73X ½" GoldTL™ Telecentric Lens, Relative Illumination Plot




#58-256, 0.73X ½" GoldTL™ Telecentric Lens, Telecentricity Plot




#58-256, 0.73X ½" GoldTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 110mm Working Distance, f6



#58-256, 0.73X ½" GoldTL™ Telecentric Lens, Depth of Field Plot, 110mm Working Distance, f6



#58-256, 0.73X 1/2" GoldTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 110mm Working Distance, f10



#58-256, 0.73X 1/2" GoldTL™ Telecentric Lens, Depth of Field Plot, 110mm Working Distance, f10

Stock No.	A	B	C	D	E	F	G
#56-024	88mm	16mm	34mm	94mm	120mm	101.6mm	50mm
#56-025	85mm	17.5mm	32.5mm	91mm	120mm	101.6mm	48.5mm
#56-026	103mm	—	39.5mm	107mm	103mm	90mm	55.5mm
#56-027	134mm	—	55mm	148mm	134mm	122mm	81mm

