


0° AOI 25mm Dia, Cold Mirror



Stock **#43-844** CLEARANCE **20+ In Stock**

-

1

+

A\$24⁴⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$24.40 each
Need More?	Request Quote

Product Downloads

General	
	Type:
Cold Mirror	
Physical & Mechanical Properties	
	Diameter (mm):
25.00	
	Thickness (mm):
3.30	
	Dimensional Tolerance (mm):
±0.25	

Optical Properties	
0.00	Angle of Incidence (°):
Cold Mirror, 0°	Coating:
BOROFLOAT®	Substrate: □
80-50	Surface Quality:
Coating Specification: R _{avg} >90% @425 - 675nm T _{avg} >85% @800 - 1200nm	
425 - 1200	Wavelength Range (nm):
4 - 6λ	Surface Flatness (P-V):
Dielectric	Coating Type:


Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- 0° and 45° Angle of Incidence Options Available
- Reflects 90% of Visible Light
- Transmits 80% of the NIR and IR

These Cold Mirrors have a 0° and 45° angle of incidence and are ideal for decreasing the undesirable heat caused by infrared radiation. A multi-layer dielectric coating reflects 90% of visible light while transmitting over 80% of the NIR and IR. Cold Mirrors function satisfactorily with resistance to damage from ambient temperatures of -45°C to +232°C and are ideal for projection systems, where heat build-up can lead to system damage. Made of BOROFLOAT® glass, these Cold Mirrors can be cut to the desired size for any application.

Technical Information



Compatible Mounts