

[See all 12 Products in Family](#)

1-1.75mm, 24-14TPI, Screw Thread Micrometer Anvil/Tip Set

See More by [Mitutoyo](#)



Stock #78-308 **1 In Stock**

- 1 + A\$161⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$161.60 each
Need More?	Request Quote

Product Downloads

General

24 - 14 TPI, 1 - 1.75mm **Range:**

V Anvil and Conical Spindle **Type:**

126-803 **Model Number:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Available as Standard, Blade Micrometer, or with Interchangeable Anvils
- Measurement Ranges from 0 – 6"
- Baked Enamel Finish on Frame for Durability

Mitutoyo Mechanical Micrometers provide quick and accurate external measurements and are available in several form factors to best suit the application. The Uni-Mke Micrometer features interchangeable anvils ranging from 0-1" for measuring tube thickness, rivet head heights, and shoulder-edge distances. The non-rotating spindle type blade micrometer utilizes a blade anvil and spindle to reach difficult to measure areas and reduce torsion on softer parts, making it ideal for grooves and keyways. Mitutoyo Mechanical Micrometers feature a ratchet stop or friction thimble to provide uniform pressure on a workpiece for precise, repeatable measurements. These micrometers are designed with a baked enamel finish and carbide facing on the spindles and anvils for enhanced durability and longer lifespan.

;