

## 1" Length, 1/4-20 and 1/4-20, Steel Post



Stock #72-791 NEW 6 In Stock

A\$9<sup>20</sup>

ADD TO CART

Volume Pricing	
Qty 1+	A\$9.20 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

English Type:

**Physical & Mechanical Properties**

±0.1 Length Tolerance (mm):

1 Length (inches):

25.40 Length (mm):

Diameter (inches):

0.5

12.70

**Diameter (mm):**

-0.02/-0.05

**Diameter Tolerance (mm):**

## Threading & Mounting

**Male Thread:**

Thread 1: 1/4 - 20  
Thread 2: 1/4 - 20

## Regulatory Compliance

**RoHS 2015:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

**Reach 247:**

[Compliant](#)

## Product Details

- English or Metric Versions Options Available
- Wide Variety of Lengths Available from 25.4 to 304.8mm (1" to 12").
- Removable Top and Bottom Set Screws Available

Stainless Steel Optical Mounting Posts are a practical and straightforward way to integrate optical assemblies and photonic equipment onto an [optical lab table](#) or [breadboard](#). All mounting posts are 12.7 mm (0.5") in diameter and are offered in various lengths from 25.4 to 304.8mm (1" to 12"). Each mounting post features a female thread on each end with a set screw preinstalled, making it simple to mount components with counterbore or tapped hole mounting features. Stainless Steel Optical Mounting Posts can be used with [Post Holders](#) to allow for height adjustment of the optical component, and for a secure connection with the optical benchtop. Thread values (M4 x 0.7/M6 x 1.0 for Metric; 8-32<sup>1/4</sup>-20 for English) are laser-engraved on the ends of each post for quick identification and integration.

**Note:** All posts have a through-hole that allows an Allen wrench, 5.5mm or 7/32" key size, or other tools to rotate the post easily.