


**TECHSPEC® 0° AOI, 35.0mm Square, Cold Mirror**



TECHSPEC High Performance Cold Mirrors

Stock **#64-439** **15 In Stock**

- 1 + A\$125<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	A\$125.60 each
Qty 10-25	A\$113.60 each
Qty 26-49	A\$107.20 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Cold Mirror **Type:**

**Physical & Mechanical Properties**

3.30 ±0.2 **Thickness (mm):**

35.0 x 35.0 **Dimensions (mm):**

Dimensional Tolerance (mm):

+0.0/-0.2

Length (mm):

35.00

Width (mm):

35.00

## Optical Properties

Transmission (%):

Longpass Filter

Coating Type:

Dielectric

Coating:

Cold Mirror, 0°

Surface Flatness (P-V):

4 - 6λ

Wavelength Range (nm):

400 - 1150

Substrate:

**BOROFLOAT®**

Angle of Incidence (°):

0

Coating Specification:

$R_{avg} \geq 95\%$  @ 400 - 690nm and  $T_{avg} \geq 90\%$  @ 750 - 1200nm

AR Coating:  $R_{avg} < 1\%$  @ 700 - 1150nm

Surface Quality:

80-50

## Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 247:



Compliant

## Product Details

- >95% Reflection from 400 - 690nm
- >90% Transmission from 750 - 1200nm
- Optimized for 0° or 45° Angle of Incidence

TECHSPEC® High Performance Cold Mirrors feature a multi-layer dielectric coating optimized for greater than 95% reflection of visible light and greater than 90% transmission of IR wavelengths. Cold mirrors are designed for use in any application where heat build-up can cause damage or adverse effects. For high power illumination, forced air cooling is recommended.

## Technical Information



Quote Your Size

## Compatible Mounts

---

;