

1.8mm - 3.6mm Focal Length, Varifocal Video Lens



1.8mm-3.6mm FL, Varifocal Video Lens, #55-254

Stock **#55-254** **5 In Stock**

-

1

+

A\$481⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$481.60 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Type:

Varifocal Lens

Physical & Mechanical Properties

Length (mm):

51.00

37.4	Maximum Diameter (mm):
0.0	Maximum Rear Protrusion (mm):
Optical Properties	
1236 - 332	Field of View @ Min Working Distance (mm):
144.2° - 79.4°	Horizontal Field of View, 1/3" Sensor:
1.8-3.6	Focal Length Range (mm):
200 - ∞	Working Distance (mm):
f/1.6 - f/16	Aperture (f/#):
VS	Lens Wavelength Range:
Sensor	
1/3"	Maximum Sensor Format:
Threading & Mounting	
CS-Mount	Mount:
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

PRODUCT DETAILS

CS-mount lenses are not compatible with C-mount cameras.

- Large Field of View
- C and CS-Mount Lenses

Varifocal Imaging Lenses provide a flexible solution to applications that previously would have required multiple fixed focal length lenses. Simply adjust through the indicated focal length range for the desired field of view within the specified working distance range, and then set the focus for the best image. Due to the variable focal length range, varifocal lenses are also known as vari-focal, variable-focus, or multi-focal lenses. Varifocal Imaging Lenses can select the focal length within the specified range, like zoom lenses, but unlike a zoom lens, focus adjustment is needed after setting of the focal length. They have a different, simplified optical and mechanical design that is more cost-efficient to produce than zoom lenses. The focal length adjustment is typically a middle or rear assembly of elements that slide back and forth, whereas the separate focus adjustment is typically a front cell movement.

#57-680 is a high-resolution, low-distortion lens for MegaPixel cameras.

Note: CS-mount lenses are not compatible with C-mount cameras.

TECHNICAL INFORMATION

