

[See all 4 Products in Family](#)

## Siemens Star Target, 4" x 4", 120 Sectors Photo Paper



Photo Paper Star Target

Stock #46-246 **9 In Stock**

⊖ 1 ⊕ A\$275<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-4	A\$275.20 each
Qty 5+	A\$261.92 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Emulsion Coated **Note:**  
No **NIST Certification:**

#### Physical & Mechanical Properties

0.033 - 0.818 **Line Width (mm):**  
**Number of Sectors:**

120.00

62.5 **Pattern Diameter (mm):**

4 x 4 ±0.004 **Dimensions (inches):**

0.20 ±nominal **Thickness (mm):**

### Optical Properties

0.6112 - 15.28 **Frequency (lp/mm):**

Photo Paper **Substrate:**

>1.6 **Optical Density OD (Average):**

3° **Wedge Angle (°):**

2.5 **Unresolved Core Diameter (mm):**

### Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 235:**

## Product Details

- Ideal for Detection of Focus Errors and Astigmatism
- Frequency Range at Target Center (lp/mm) 7.14 - 229.2
- Available on White Photographic Paper or Chrome on Glass

Star Targets are ideal for identifying focus errors, astigmatism, and other aberrations existing in an imaging system. Our 60mm diameter ([#58-832](#) and [#58-833](#)) targets feature an unresolved core of 100µm and are ideal for high-resolution or high magnification imaging systems. Both targets are chrome on glass. Star Targets, in the 4" x 4" size, are available as chrome on glass ([#46-247](#)) or photo paper ([#46-246](#)), feature an unresolved core of 2.7mm, and are designed for mid- to low-range spatial frequencies common in macro imaging systems. These targets have a frequency range at target center (lp/mm) of 7.14-229.2.