

[See all 69 Products in Family](#)

## TECHSPEC® 10 x 10 x 1.75mm Thickness, MgF<sub>2</sub> Coated, BOROFLOAT® Window

See More by [SCHOTT Optical Components](#)



TECHSPEC BOROFLOAT Borosilicate Windows

Stock **#83-371** **2 In Stock**

A\$50<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	A\$50.40 each
Qty 6-25	A\$40.00 each
Qty 26-99	A\$36.80 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Protective Window **Type:**

Glass **Type of Window:**

### Physical & Mechanical Properties

**Clear Aperture CA (mm):**

9.00 x 9.00	
10.00 x 10.00	<b>Dimensions (mm):</b>
1.75 ±0.2	<b>Thickness (mm):</b>
10.00	<b>Length (mm):</b>
10.00	<b>Width (mm):</b>
±0.5	<b>Dimensional Tolerance (mm):</b>
Protective as needed	<b>Bevel:</b>
≥90	<b>Clear Aperture (%):</b>
Seamed	<b>Edges:</b>
0.20	<b>Poisson's Ratio:</b>
64	<b>Young's Modulus (GPa):</b>
480.00	<b>Knoop Hardness (kg/mm<sup>2</sup>):</b>

## Optical Properties

MgF <sub>2</sub> (400-700nm)	<b>Coating:</b>
<b>BOROFLOAT®</b>	<b>Substrate:</b> □
1.472	<b>Index of Refraction (n<sub>d</sub>):</b>
80-50	<b>Surface Quality:</b>
≥95	<b>Transmission (%):</b>
65.41	<b>Abbe Number (v<sub>d</sub>):</b>
R <sub>abs</sub> ≤2.5% @ 550nm	<b>Coating Specification:</b>
400 - 700	<b>Wavelength Range (nm):</b>
4 - 6λ	<b>Surface Flatness (P-V):</b>

## Material Properties

2.23	<b>Density (g/cm<sup>3</sup>):</b>
525	<b>Transformation Temperature (°C):</b>
3.25 (+20 to +300°C)	<b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b>

## Environmental & Durability Factors

1 hour @ 500; >100 hours @ 450	<b>Operating Temperature (°C):</b>
Short Term, 1 hr: 110K 1 - 100 hrs: 90K Long Term, >100 hrs: 80K	<b>Resistance to Temperature Difference (K):</b>
Up to 4mm Thick: 175K 4 - 6mm Thick: 160K 6 - 15mm Thick: 150K	<b>Thermal Shock (K):</b>

## Regulatory Compliance

<b>Compliant</b>	<b>RoHS 2015:</b>
<b>View</b>	<b>Certificate of Conformance:</b>
<b>Compliant</b>	<b>Reach 247:</b>


## Product Details

- Low Coefficient of Thermal Expansion
- Visible to Near Infrared Transmission
- High Resistance to Thermal Shock

TECHSPEC® BOROFLOAT® Borosilicate Windows are ideal for high temperature and harsh environment applications. The windows have a low coefficient of thermal expansion of 3.25 (+20 to +300°C). TECHSPEC® BOROFLOAT® Borosilicate Windows feature visible to near infrared transmission. Unlike common borosilicate that is drawn flat, BOROFLOAT® is produced by a float technique that yields superior surface flatness — typically 4 - 6λ per inch. BOROFLOAT® is about three times more resistant to thermal shock than standard soda lime glass.

Can't find what you need? Get a quick [custom quote](#).

## Technical Information



### Coating Curves

### Quote Your Size

### Compatible Mounts