

10 x 10mm, 250µm Pitch, 6° Div., Cyl. Microlens Array UV-VIS



Stock #72-598 **2 In Stock**

A\$1,498⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	A\$1,498.00 each
Qty 11-25	A\$1,203.00 each
Qty 26-49	A\$1,124.00 each
Need More?	Request Quote

Product Downloads

General

Lens Array Type:

Physical & Mechanical Properties

10.0 x 10.0 ±0.05 Dimensions (mm):

0.711 Radius R (mm):

1.20 ±0.05 **Thickness (mm):**

Optical Properties

1.60 **Effective Focal Length EFL (mm):**

Substrate:
[Fused Silica](#) (Corning 7980)

UV-NIR (250-700nm) **Coating:**

250 - 700 **Wavelength Range (nm):**

Coating Specification:
 $R_{\text{abs}} \leq 1.0\%$ from 350 - 450nm @ 0° AOI
 $R_{\text{avg}} \leq 1.5\%$ @ 250 - 700nm @ 0°

±6 **Divergence Angle (°):**

250.00 ±0.25 **Pitch (µm):**

Single-Sided **Array Type:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 250:**

Product Details

- Generate Non-Gaussian Line Patterns
- Ideal for Light Homogenization
- Excellent Performance from 193nm – 2.5µm

Cylindrical Microlens Arrays are used to homogenize a variety of light sources, including lasers or high power LEDs. Unlike [Square Microlens Arrays](#), which generate spot patterns, Cylindrical Microlens Arrays yield non-gaussian line patterns, and are ideal for welding, drilling, or laser ablation applications from the UV to IR. Cylindrical Microlens Arrays are available uncoated, VIS-NIR, or UV-NIR coated, including options with lenses on a single side for line generation applications or double-sided (with cross-oriented lenses) for beam homogenisation. Additionally, these lenses can be used as fast axis collimators.