

1000mm Travel, High Load Capacity, Motorized Linear Stage, Integrated Controller with Encoder

See More by [Zaber™](#)



Zaber™ High Load Capacity Motorized Linear Stage

Stock **#25-175** **2 In Stock**

-

1

+

A\$9,136^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	A\$9,136.00 each
Need More?	Request Quote

Product Downloads

General	
Type:	Metric
Encoder:	Yes
Manual Control/ LED Indicators:	Yes
Manufacturer:	Zaber Technologies Inc.

Note: Requires a 24-48 VDC power supply and either #15-295 for USB connectivity or #15-297 for RS-232 connectivity. A data cable (#15-296 or #15-299) can be used to daisy chain multiple stages together to control simultaneously.	
Stepper (2 Phase)	Type of Motor:
Rotary	Encoder Type:
Quadrature Encoder	

Physical & Mechanical Properties

Linear (X)	Type of Movement:
Recirculating Ball Linear	Guide System:
1317.6 x 131.0	Stage Size (mm):
1000mm	Travel (mm):
450 (unidirectional)	Accuracy (µm):
<25	Backlash (µm):
57.2	Height (mm):
510	Load Capacity (kg):
<4	Repeatability (µm):
0.0002 to 110	Speed (mm/s):
1200	Thrust (N):
8.393	Weight (kg):
400 CPR	Encoder Resolution:
120	Cantilevered Load Capacity (N□m):

Optical Properties

0.390625	Resolution (µm):
----------	-------------------------

Electrical

3600	Maximum Operating Current (mA):
------	--

Hardware & Interface Connectivity

Precision Ball Screw	Type of Drive:
24-48 VDC	Power Supply:
RS-232 with #15-297	Computer Interface:

Environmental & Durability Factors

0 - 50	Operating Temperature (°C):
--------	------------------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- High Load Capacity of 510kg
 - 500 and 1000mm Travel Options
 - Integrated Controller and Encoder with 400 Counts per Revolution (CPR)
- Zaber™ High Load Capacity Motorized Linear Stages feature a load capacity of 510kg (5003N) making them ideal for factory automation applications where precise linear adjustments of heavy components are necessary. These

stages include a rotary quadrature encoder integrated into the stepper motor with 400 Counts per Revolution (CPR), as well as closed-loop control and slip/stall detection and recovery. Zaber™ High Load Capacity Motorized Linear Stages have an indexed knob providing versatility of analog control in the absence of digital input, as well as a flexible stainless steel dust cover to prevent the ingress of small particulates.

Note: A 24-48 VDC universal power supply (required), data cables for daisy chaining, and computer interface cables (USB or RS-232) are sold separately.