

[See all 12 Products in Family](#)

## 100µm Aperture Diameter, Chrome on Glass Aperture



Stock #90-738 NEW **3 In Stock**

-
1
+
A\$296.<sup>00</sup>

ADD TO CART

### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1+     | A\$296.00 each                |
| Need More? | <a href="#">Request Quote</a> |

### Product Downloads

### Physical & Mechanical Properties

Outer Diameter (mm):  
25.4

Fixed Aperture Diameter (µm):  
100 ±3.0

Thickness (inches):  
0.06 ±0.004

Thickness (mm):  
1.52

Thickness Tolerance (mm):  
±0.1

## Optical Properties

Low Reflective Chrome

Coating:

## Regulatory Compliance

[View](#)

Certificate of Conformance:

## Product Details

- Chrome Coating on Glass Substrate
- Ideal for Precise Beam Control, Modulation, or Optical Alignment
- Pinhole Diameters Ranging from 10 $\mu$ m to 1,000 $\mu$ m

Chrome Coated Glass Optical Apertures are composed of soda lime float glass with low reflective chrome coating for high-contrast performance. These apertures are designed with pinhole diameters ranging from 10 $\mu$ m to 1000 $\mu$ m. The apertures have an overall diameter of 25.4mm (1") and a thickness of 1.52mm, ensuring easy integration with a wide variety of optical mounts. Chrome coating on glass provides a stable and circular aperture diameter immune to bending or creasing. Chrome Coated Glass Optical Apertures are designed to provide high-precision light control, ideal for beam shaping, spatial filtering, and alignment in advanced photonic systems.